Rugged Belt Drive Vacuum Pumps | DUOSEAL®









 $C \in$

 Model
 Models
 Model
 Models

 1400
 1405 / 1402
 1376
 1397 / 1374

Specifications			Two-Stage Va	acuum Pumps			
Model	1400	1405	1402	1376	1397	1374	
Free Air Displacement							
cfm	0.9	3.2	5.6	10.6	17.7	23	
l/min.	25	90	160	300	500	650	
Ult. Vac. Pressure, torr (mbar) 1,2	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	
Gas Ballast	Yes	Yes	Yes	Yes	Yes	Yes	
Discharge Pressure (PSIG)							
Pump RPM	580	525	525	525	400	510	
Motor Horsepower (watts)	1/3 (250)	1/2 (370)	1/2 (370)	1 (750)	1 (750)	1-1/2 (1120)	
Oil Capacity, qt.(liters)	0.62 (0.59)	2.25 (2.1)	2.25 (2.1)	2.5 (2.4)	1.25 (1.2)	1.25 (1.2)	
Tubing Needed, I.D. in.	7/16 (11)	7/16 (11)	13/16 (21)	13/16 (21)	1-5/8 (41)	1-5/8 (41)	
Intake, Nipple Thread	3/4-20	1-20	1-20	1-20	1.75-20	1.75-20	
Exhaust, Thread Type	3/4-20	1-20	1-20	1-20	1.75-20	1.75-20	
Weight, lbs. (kg)	58 (26)	112 (51)	112 (51)	156 (71)	205 (93)	220 (100)	
Overall Dimensions LxWxH in.(cm)	17.8×9×12.6 (45.1×32.1×31.8)	20x12x15 (51x30.5x60)	20x12x15 (51x30.5x60)	20x14.1x15.4 (51x35.9x39)	26x13.7x18.8 (66x34.8x47.6)	26x13.7x18.8 (66x34.86x47.6)	
Ship Weight, lbs. (kg)	70 (31.8)	132 (60)	132 (60)	180 (81.8)	213 (96.8)	215 (97.7)	
Shipping Carton Dimensions LxWxH in.(cm)	20.5x13.8x14.5 (52.1x35.1x36.8)	22.5x15.5x19.5 (57.2x39.4x49.5)	22.5x15.5x19.5 (57.2x39.4x49.5)	22x18x19 (55.9x45.7x48.3)	27.3x18x22 (69.3x45.7x55.9)	27.3x18x22 (69.3x45.7x55.9)	
Ordering Information 3.4							
Wired for 115V, 60Hz, 1 Ph with N. American 115V Plug	1400B-01	1405B-01	1402B-01	1376B-01	1397B-01	1374B-01 ⁵	
Wired for 230V, 60Hz, 1 Ph with N. American 230V Plug	1400C-01	1405C-01	1402C-01				
Wired for 220V, 50Hz, 1 Ph w/Cont. Euro. (Schuko) Plug	1400C-02	1405C-02	1402C-02	1376C-03	1397C-03		
Explosion Proof Motor, 115V, 60 Hz	1400W-01	1405W-01	1402W-01				
3-Phase Motor 230V, 460V, 60Hz			1402M-01	1376M-01	1397M-01	1374M-01	
Wired for 115V, 60Hz, 1 Ph with N. American 115V Plug, CSA	1400B-80	1405B-80	1402B-80		1397B-80		

Applications

		page
1.	Freeze Drying	17
2.	Glove Box	26
3.	Vacuum Manifold /	
	Schlenk Line	11
4.	Vacuum Ovens	23
5.	Refrigeration Servicing	24 - 25

DUOSEAL Pumps

Rugged oil-seal pumps for a wide variety of vacuum needs, including Schlenk drying lines, freeze drying, degassing, concentrations, distillations, and more. Pulley drive enables low pump rpm operation – reduces friction, oil temperature, and oil degradation. Large oil reservoir minimizes

contamination effects and extends maintenance intervals. Use of a cold trap is recommended to protect the pump and enhance vacuum levels.

Refrigeration Servicing Pumps

Special Welch DuoSeal pumps are fitted with components designed to with stand refrigerant contact. Models 1402B-46 and 1397B-46 include integrated handles.

Note

- Two-stage pumps should not be operated continuously at pressures above 10 torr.
 Ultimate pressure measured with a trapped McCleod gauge.
- McCleod gauge.

 2. One-stage pumps should not be operated continuously at pressures above 50 torr.

Rugged Belt Drive Vacuum Pumps | DuoSeal®, CAPTURE









Model 1402B-46

Model 1376B-46 Model CRR-1A

One-Stage Vacuum Pumps						CAPTURE Refrigeran	
	w/o plate	w/bell jar plate	w/o plate	Refri	geration Servicing F	Pumps	Recovery
	1399	1399N	1380	1402B-46	1376B-46	1397B-46	CRR-1A
	1.2	1.2	5.6	5.6	10.6	17.7	10.6
	35	35	160	160	300	500	300
	1.5 x 10 ⁻² (0.019)	1.5 x 10 ⁻² (0.019)	1.5 x 10 ⁻² (0.019)	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	1 x 10 ⁻⁴ (0.00013)	3x10 ⁻² (0.04)
	No	No	Yes	Yes	Yes	Yes	
							30
	750	750	535	525	525	400	525
	1/3 (250)	1/3 (250)	1/2 (370)	1/2 (370)	1 (750)	1 (750)	1 (750)
	0.5 (0.47)	0.5 (0.47)	3.7(3.5)	2.25 (2.1)	2.5 (2.4)	1.25 (1.2)	2.5 (2.4)
	7/16 (11)	7/16 (11)	13/16 (21)	3/4" ID Flare	3/4" ID Flare	Note 7	
	3/4-20	3/4-20	1-20	1-20	1-20	1.75-20	1 NPT
	3/4-20	3/4-20	1-20	1-20	1-20	1.75-20	1 NPT
	51 (23)	63 (28.6)	91(41)	112 (51)	156 (71)	205 (93)	122 (55.4)
	17×9×10 (43.×23×25)	17x9x10 (43.x23x25.)	20x12x15 (51x31X38)	20x12x15 (51x30.5x60)	20x14.1x15.4 (51x35.9x39)	26x13.7x18.8 (66x34.8x47.6)	19.25x12.3x11.1 (48.9x31.3x28.1)
	62 (28.2)	74 (33.6)	116 (53)	132 (60)	180 (81.8)	213 (96.8)	136 (61.8)
	21x14x15 (52x35x37)	21x14x15 (52x35x37)	23x15x18 (56x38x47)	23x16x20 (57x39x50)	22x18x19 (56x46x48)	28x18x22 (69x46x56)	22x15x18 (56x38x46)
	1399B-01	1399N-01	1380B-01	1402B-46	1376B-46	1397B-46	CRR-1A
	1399C-02			1402C-46	1376C-46	1397C-46	CRR-1B
		1399B-80					

3. All 115V and 230V single phase motors include thermal overload

- protection.

 4. Models 1400C-02, 1405C-02 and 1402C-02 provided with CE marking.
- Conduit wiring installation required. No cord, plug or switch provided.
- No Cord, ping or switch pro 6. CSA approved models are 1400B-80, 1405B-80 and 1402B-80. 7. 1-1/2" NPT Female

DuoSeal™ Vacuum Pump Oil

Tested to high vacuum levels, this oil meets rigid requirements for vapor pressure, stability and viscosity.

Size	CAT. No.
Quart	1407K-11
Gallon	1407K-15
5 Gallon	1407K-20



Exhaust Filter

A replaceable filter element captures oil mist from the exhaust port of the pump and reduces pump noise.

Pump	CAT. No.
1399, 1400	1417
1376, 1402, 1405	1417P-10
1397, 1374	1417P-20

For a Complete System

i oi a compicio	0,000
Component	page
• Traps	69
• Inlet / Exhaust Accessoies	69 - 71
• Fittings / Hose	66 - 68
• Gauges	76 - 77
• Regulators / Controllers	75 - 76
Service Kits	81
• Oil	72 - 73

Capture Pump | Refrigerant Recovery & Transfer



Model CRR-1A

- Continuous discharge pressure to 30 psig(2.1 Bar)
- Pump shell rated to 100 psig (2.1 Bar)
- Minimal loss of pumping efficiency below 29.9" Hg (1000 microns/1.3 mbar)
- High flow rate of 10.6 cfm(300 lpm)
- · Durable cast iron construction
- Proven dependability

The CAPTURE pump has been specifically designed for refrigerant recovery and recycling systems requiring chiller evacuation to 29.9 in. Hg(1000 micron/1.3 mbar) while subsequent boosting of refrigerant vapor to a holding tank to 30 psig(2.1 Bar). CAPTURE pumps are the heart of transportable recovery systems used for recovering low and medium pressure refrigerants, such as R-123 and R-11.

Recovery with the CAPTURE pump can be configured in a recovery system to employ the liquid-vapor method. The first step is the recovery cylinder is evacuated with the CAPTURE pump and that pulls the refrigerant from chiller into the cylinder. Once

the liquid refrigerant is recovered, valves are switched on the recovery system, so that the remaining vapor in chiller is evacuated by the pump and boosted into chiller. The CAPTURE pump then reaches vacuum pressure levels in chiller that are required by the Clean Air Act.

Pump oil separation from refrigerant vapor and return to pump is accomplished by attaching a standard float actuated oil return found in refrigerators. The oil separator is a proven technology that minimizes pump oil loss even for very large refrigerant systems. DUOSEAL pump oil, CAT no. 1407K-11, is recommended lubricant to operate the CAPTURE pump.

Specifications				
Model	CRR-1			
Free Air Displacement				
cfm(lpm)	10.6 (300)			
Ult. Vac. Pressure, torr (mbar)	3x10 ⁻² (0.04)			
Max Vacuum, in Hg	29.9+			
Discharge Pressure, psig(bar)	30 (2.1)			
Pump RPM	525			
Motor Horsepower (watts)	1(750)			
Oil Capacity, qt. (liters)	2.5(2.4)			
Intake thread, NPT in.	1			
Exhaust thread, NPT in.	1			
Weight, lbs (kg)	112(55.5)			
Overall dimensions LxWxH in.(cm)	19.3x12.3x11.1 (49x31.2x28.2)			
Ship Weight, lbs. (kg)	170((77.3)			
Shipping Carton Dimensions LxWxH in. (cm)	20x14.1x15.4 (55.9x45.7x48.3)			
Ordering Information				
Wired for 115V, 60Hz, 1 Ph with N. American 115V plug	CRR-1A			
Wired for 230V, 50Hz, 1 Ph w/Cont. Euro. (Schuko) plug	CRR-1B			
Mounted pump on base with guard, but without motor	CRR-1C			