

Swing-out Rotor, GRS-L-r250-4

4 loadings
 $\angle 90^\circ$



Rectangular 250 ml Bucket GLB-r250-r250

Bucket bore (w x d x h, mm)
 : 86 x 70.3 x 102.5
 Radius (mm) : 175.2
 Max.RPM : 4,000
 Max.RCF (g-force) : 3,134
 Max.height for tube fit (mm) : 130


Tube											
Tube capacity (ml)	1.5/2.0	3	5	10	15	15 ml conical	50	50 ml conical	15	85	250
Tube rack											
Cat. No.	GAM-m2.0-20 (r250)	GAM-5-12(r250)	GAM-5-12(r250)	GAM-15-12(r250)	GAM-15-12(r250)	GAM-c15-9 (r250)	GAM-50-4 (r250)	GAM-c50-3 (r250)	GAM-85-2(r250)	GAM-85-2(r250)	GAS-250(r250)
Rack capacity (ea/4)	20/80	12/48	12/48	12/48	12/48	9/36	4/16	3/12	2/8	2/8	1/4
Hole dimension (Φ x L, mm)	11.3 x 39	13.5 x 58	13.5 x 80	17.5 x 90	17.5 x 90	17.5 x 90	30.2 x 90	30.5 x 90	17 x 86.5	38.5 x 86.5	62.5 x 87



Microplate Holder GLP-mw-r250

Holder bore (w x d x h, mm)
 : 88 x 128.5 x 80
 Radius (mm) : 153
 Max.RPM : 4,000
 Max.RCF (g-force) : 2,737

Plate		
Plate capacity (ml)	MTP	DWP
Holder capacity (ea/4)	4/16	1/4



100 ml Bucket GLB-100(L)-r250

Bucket bore (Φ x L, mm) : 35.5 x 180.6
 Radius (mm) : 243.6
 Max.RPM : 4,000
 Max.RCF (g-force) : 4,358
 Max height for tube fit (mm) : 207

Glass	
Glass capacity (ml)	100



100 ml Bucket GLB-100(S)-r250

Bucket bore (Φ x L, mm) : 44.6 x 143.3
 Radius (mm) : 232.3
 Max.RPM : 4,000
 Max.RCF (g-force) : 4,155
 Max height for tube fit (mm) : 190

Glass	
Glass capacity (ml)	100



100 ml Bucket GLB-100(C)-r250

Bucket bore (Φ x L, mm) : 61.5 x 145.3
 Radius (mm) : 234.3
 Max.RPM : 4,000
 Max.RCF (g-force) : 4,191
 Max height for tube fit (mm) : 190

Glass	
Glass capacity (ml)	100