



## ORBi-SHAKER™ CO<sub>2</sub>

Remote Controlled, All Environment Shakers

- Designed to fit and maximize capacity in most CO<sub>2</sub> incubators and chambers
- Remote controlled, adjust settings without disturbing the CO<sub>2</sub> environment
- Instantly exchange flask clamps with MAGic Clamp™ accessories

CE

The new Orbi-Shaker CO<sub>2</sub> series is designed for shaking, mixing & aeration applications in extreme environments, including CO<sub>2</sub> incubators. It can withstand temperatures from 0 to 65°C and humidity levels up to 100%.

To avoid contamination, unintentional release of gas or deviations from protocol, all settings are adjusted via the included remote control module. This module can be stored outside of the chamber and connects to the shaker via a flat (1mm thickness) cable, that easily passes through a port or underneath an incubator door without compromising the seal. This allows for user adjustment of run time or mixing speed without opening the chamber door(s).

The instrument is supplied with a non-slip rubber mat platform. In addition, convenient MAGic Clamp™ platforms (of multiple sizes) are also available for use with Erlenmeyer flasks and test tube racks. The unique magnetic attachment method has been widely recognized as the easiest way to instantly change between flask clamps of different sizes.



Remote controller adjusts shaker settings from outside of the chamber and magnetically attaches to most incubators



H1000-MR-CMB Adjustable flask clamp, accepts 125ml, 250ml and 500ml Erlenmeyer flasks. (For a video demonstration, scan the QR code above.)



Video Demonstration



### Maximum Flask Capacity with MAGic Clamp Platforms

| Item No.      | Description:  | Platform H1000-MR             | Platform BT3000-MR   | Platform H1010-MR                               |
|---------------|---|-------------------------------|--|---|
|               |   | Available For Orbi-Shaker JR. | Available For Models Orbi-Shaker & Orbi-Shaker CO <sub>2</sub> | Available For Orbi-Shaker XL (CO <sub>2</sub> ) |
| H1000-MR-CMB  | NEW! Adjustable flask clamp, accepts 125, 250 & 500ml Erlenmeyer flasks | 12/8/5                        | 20/14/9  | 36/25/16  |
| H1000-MR-50   | Flask clamp, 50ml Erlenmeyer flask                                      | 20                            | 30   | 49  |
| H1000-MR-125  | Flask clamp, 125ml Erlenmeyer flask                                     | 12                            | 20   | 36  |
| H1000-MR-250  | Flask clamp, 250ml Erlenmeyer flask                                     | 8                             | 14   | 25  |
| H1000-MR-500  | Flask clamp, 500ml Erlenmeyer flask                                     | 5                             | 9  | 16  |
| H1000-MR-1000 | Flask clamp, 1L Erlenmeyer flask  | 4                             | 5  | 9   |
| H1000-MR-2000 | Flask clamp, 2L Erlenmeyer flask  | 1                             | 2  | 5   |
| H1000-MR-3000 | Flask clamp, 3L (or 2.8L) Fernbach flask                                | N/A                           | 1  | 4   |

| Compatibility Chart:                                 | SureTherm™ CO <sub>2</sub> |      | New Brunswick™ |             | Shel Lab®   | Thermo® HeraCell™ |     | Fisher®      | VWR® Symphony™ |      |
|--|----------------------------|------|----------------|-------------|-------------|-------------------|-----|--------------|----------------|------|
|  | 45L                        | 180L | Galaxy® S4fi   | Galaxy® 170 | 142L & 167L | 150               | 240 | IsoTemp™ 184 | 6.3A           | 8.5A |
| Orbi-Shaker CO <sub>2</sub> (14 x 12" platform)      | *                          | ○    | ○              | ○           | ○           | ○                 | ○   | ○            | ○              | ○    |
| Orbi-Shaker CO <sub>2</sub> XL (16 x 16.5" platform) | N/A                        | ○    | N/A            | ○           | ○           | ○                 | ○   | ○            | ○              | ○    |
| Orbi-Shaker CO <sub>2</sub> XL (18 x 18 platform)    | N/A                        | N/A  | N/A            | N/A         | ○           | N/A               | ○   | ○            | N/A            | ○    |

\* Compatible 9.5 x 11.5" (Item: H1000-MR) available



|                         |  |
|-------------------------|--|
| Speed Range:            | Variable, 30 to 300 rpm                |
| Speed Increment:        | 1 rpm                                  |
| Motion / Orbit:         | Orbital / 19mm                         |
| Max. Capacity (BT4001): | 1 x 2L or 5 x 1L                       |
| Max. Capacity (BT4011): | 5 x 2L or 9 x 1L                       |
| Timer:                  | 1 min. to 99 hr / Continuous           |
| Platform Dimensions:    |  |
| BT4001 (included):      | 13 x 12 in. / 33 x 30 cm               |
| BT4011 (included):      | 16 x 16.5 in. / 40 x 42.5 cm           |
| Operating Temp. Range:  | 0°C to +65°C                           |
| Dimensions: W x D x H   |  |
| BT4001 Shaker:          | 11.9 x 13.4 x 3.5 in. / 30 x 34 x 9 cm |
| BT4011 Shaker:          | 17 x 18 x 5 in. / 43 x 45.75 x 12.7 cm |
| Weight (BT4001)         | 25 lbs, (11.5kg)                       |
| Weight (BT4011):        | 50lbs (23kg)                           |
| Cord Length:            | 60.5 in. / 154 cm                      |
| Electrical:             | 120 or 230V, 50-60Hz, 600W             |
| Warranty:               | 2 Years                                |

### Ordering Information:

| Item No.   | Description:  |
|--|---|
| BT4001*  | Orbi-Shaker CO <sub>2</sub> w/ flat mat platform (13x12 in.)      |
| BT4011*  | Orbi-Shaker CO <sub>2</sub> XL w/ flat mat platform (16x16.5 in.) |
| MAGic™ Clamp Universal Platforms for flask clamps & tube racks** |   |
| BT3000-MR  | MAGic Clamp™ platform (14x12 in.) for BT4001                      |
| BT4010-MR  | MAGic Clamp™ platform (16x16.5 in.) for BT4011                    |
| H1010-MR   | MAGic Clamp™ platform (18x18 in.) for BT4011                      |
| Additional Platforms:  |   |
| H1000-P-SP   | Universal spring platform for unique vessel types                 |
| H1000-P-MP   | Dedicated platform for 4 x microplates                            |

\*115V with US plug. For 230v (EU plug), please add (-E).

\*\*Flask clamps and tube racks sold separately, see page 31 for a complete listing.

### Maximum Capacity for MAGic Clamp Platforms (Test Tube / Microplate Racks)

| Item No.       | Description:                                    | Platform H1000-MR             | Platform BT3000-MR   | Platform H1010-MR                               |
|----------------|---|-------------------------------|--|---|
|                |   | Available For Orbi-Shaker JR. | Available For Models Orbi-Shaker & Orbi-Shaker CO <sub>2</sub> | Available For Orbi-Shaker XL (CO <sub>2</sub> ) |
| H1000-MR-T15   | Tube Rack, 15ml conical tubes, 32 x 15ml        | 2                             | 3  | 8   |
| H1000-MR-T50   | Tube Rack, 50ml conical tubes, 15 x 50ml        | 2                             | 3  | 8   |
| H1000-MR-1550  | Combi-Tube Rack, 30 x 15ml & 20 x 50ml tubes    | 2                             | 2  | 4   |
| H1000-MR-T600  | Tube/Bottle Rack, 4 x 500/600ml conical bottles | 1                             | 2  | 4   |
| H1000-MR-T15H  | Tube rack, 12 x 1.5/2.0ml tubes, horizontal     | 2                             | 4  | 6   |
| H1000-MR-T150H | Tube rack, 4 x 15ml tubes, horizontal           | 4                             | 6  | 8   |
| H1000-MR-T500H | Tube rack, 2 x 50ml tubes, horizontal           | 4                             | 6  | 8   |
| H1000-MR-MP    | Plate rack, holds one microplate                | 4                             | 6  | 8   |
| H1000-MR-TSR   | Angled tube rack holder (with adjustable tilt)  | 2                             | 6  | 8   |