

### Additional Rotors (High Speed):



**Item: Z326-0685-25**

6 x 85ml Angle Rotor (25°)  
"Super rotor" Fits 85ml, 50ml, 15ml, and 7ml

Max Speed: 11,000 rpm / 13,932 x g (Z326)  
Max Speed: 13,500 rpm / 20,984 x g (Z326K)

Accel: 40 sec. / Decel: 50 sec.

**Inserts/Adapters**

Z326-85-A15R: 15ml round  
Z326-85-A15: 15ml conical  
Z326-85-A50R: 50ml round  
Z326-85-A50: 50ml conical



**Item: Z326-0650-HS**

6 x 50ml Angle Rotor (26°) Round

Max Speed: 12,000 rpm / 13,522 x g  
Accel: 40 sec. / Decel: 30 sec.

**Inserts/Adapters**

Z326-50-A30: 30ml round  
Z326-50-A15R: 15ml (conical or round)



**Item: Z326-1050**

10 x 50ml Angle Rotor (38°) Conical

Max Speed: 7,500 rpm / 8,174 x g  
Accel: 62 sec. / Decel: 36 sec.

**Inserts/Adapters**

Z326-50-A15: 15ml conical  
Z326-50-B15: 15ml round  
C3100-ADP: 5-7ml (in 15ml adapter)



**Item: Z326-1205**

12 x 5ml Angle Rotor (45°)

Max Speed: 14,000 rpm / 18,624 x g (Z326)  
Max Speed: 15,000 rpm / 21,379 x g (Z326K)

Accel: 25 sec. / Decel: 25 sec.\*

**Inserts/Adapters**

Z216-05-C10: 1.0ml Cryo  
Z216-05-C18: 1.8ml Cryo



**Item: Z326-2010**

20 x 10ml Angle Rotor (30°)

Max Speed: 12,000 rpm / 15,775 x g  
Accel: 40 sec. / Decel: 30 sec.



**Item: Z326-2420**

24 x 1.5/2.0ml Angle Rotor with Quick-Seal lid (45°)

Max Speed: 14,000 rpm / 18,624 x g (Z326)  
Max Speed: 15,000 rpm / 21,379 x g (Z326K)

Accel: 23 sec. / Decel: 16 sec.\*



**Item: Z326-2420H**

24 x 1.5/2.0ml Angle Rotor (45°)  
Hermetically Sealed Lid

Max Speed: 14,000 rpm / 18,624 x g (Z326)  
Max Speed: 15,000 rpm / 21,379 x g (Z326K)

Accel: 23 sec. / Decel: 16 sec.\*



**Item: Z326-3020H**

30 x 1.5/2.0ml Angle Rotor (45°)  
Hermetically Sealed Lid

Max Speed: 13,000 rpm / 17,758 x g (Z326)  
Max Speed: 14,000 rpm / 20,505 x g (Z326K)

Accel: 25 sec. / Decel: 25 sec.\*



**Item: Z326-1220H**

12 x 1.5/2.0ml Angle Rotor (40°)  
Hermetically Sealed Lid

Max Speed: 18,000 rpm / 23,542 x g  
Accel: 25 sec. / Decel: 20 sec.



**Item: Z326-4420**

44 x 1.5/2.0ml Angle Rotor with Quick-Seal lid (32°/55°)

Max Speed: 15,000 rpm / 21,379 x g  
Accel: 24 sec. / Decel: 20 sec



**Item: Z326-6405**

64 x 0.5ml Angle Rotor (40°)

Max Speed: 13,500 rpm / 16,298 x g (14,261)  
Accel: 17 sec. / Decel: 12 sec



**Item: Z326-3202**

4 x 8 PCR Strips / 32 x 0.2ml (45°)  
Hermetically Sealed

Max Speed: 15,000 rpm / 15,343 x g  
Accel: 17 sec. / Decel: 12 sec

\* Acceleration and deceleration provided for the maximum speed of model Z326.

### Also Available from Benchmark:

## Z446 Series High Capacity Centrifuges

Swing Out Rotor Accepts up to:

- 56 x 15ml conical tubes
- 28 x 50ml conical tubes
- 12 x microplates

